




Product	CareSystem shower chair 410, manually height adjustable
Item number	R7165000
Colour	White
Product description	 <p>Shower chair 410 with back rest, "soft feel", seat height adjustable 340 mm. Excl. mounting kit. Discontinued as per 31/12-2015</p> <p>Shower chair 410 with back rest, "soft feel", seat height adjustable 340 mm. Excl. mounting kit. Discontinued as per 31/12-2015</p>
Adjustability	Height adjustable
Product capacity	Max. vertical load: 150 kg.
Materials	<p>Basic material: 20 micrometre anodized aluminium</p> <p>Seat/backrest: Polyurethane foam with marine ply core</p> <p>Seat/backrest surface: Gum lac</p> <p>Lever: Stainless steel w/nylon knob</p> <p>Front plate/end covers, track: Polystyrene plastic (PS)</p>
Ergonomy	<p>Soft and slip-resistant material with a warm feel.</p> <p>Ergonomically designed seat.</p>
Features	<p>The seat can fold up when not in use or to make more space.</p> <p>Height adjustable 340 mm - the height of the seat and the backrest can be adjusted separately.</p>



PRESSALIT®

Product	CareSystem shower chair 410, manually height adjustable
Item number	R7165000
Cleaning	Pressalit recommends that chalky deposits be removed from wall tracks and other aluminum parts using a solution of three parts of 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts should be wiped over with a damp cloth wrung out in clear water.

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®