



PRESSALIT®

Product Item number	Changing table, 800 x 1800 mm, electrically height adjustable, with sanitary appliances R8753000
Colour	White
Product description	<p>Discontinued per 31 Dec 2015 and replaced by R8653</p> <p>Freestanding changing table with sanitary appliances, 800 mm x 1800 mm, with electric motor with hand control incl. transformer. Incl. safety stop, stainless steel sink, tap, shower head, feed/waste system, 2 wire baskets. Height adjustable from 650 mm - 1000 mm. Excl. mounting kit.</p> <p>Discontinued per 31 Dec 2015 and replaced by R8653</p> <p>Freestanding changing table with sanitary appliances, 800 mm x 1800 mm, with electric motor with hand control incl. transformer. Incl. safety stop, stainless steel sink, tap, shower head, feed/waste system, 2 wire baskets. Height adjustable from 650 mm - 1000 mm. Excl. mounting kit.</p>
Adjustability	Height adjustable
Product capacity	Max load: 150 kg.
Speed upwards	Speed up mm: 14 mm/s Speed down mm: 14 mm/s
Noise level	48 dB
Materials	Lifting unit and baskets: Powder-laquered steel. Worktop: Melamine
Ergonomy	The smooth height adjustment ensures that it is always possible to set the table at an ergonomically correct height.
Features	Easy-to-clean surfaces ensure optimum hygiene. Underglued sink and tap with pull-out spout.
Mains connection (V)	230



PRESSALIT®

Product	Changing table, 800 x 1800 mm, electrically height adjustable, with sanitary appliances
Item number	R8753000
Actuator (motor)	2 x LA31 Deskline (Linak), 1500N, IPX1
Control box	CBD6 (Linak), IP22
Wired remote control	HB3 (Linak), IP66
Power consumption (maximum load)	Power consumption by maximum load, watt: 96 W Power consumption by standby: 0,1 W
Cleaning	The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®