




|                                      |  |
|--------------------------------------|--|
| <b>Product</b><br><b>Item number</b> | PLUS handrail corner with vertical grip 762 x 762 x 1090 mm<br>RT136000  |
| <b>Colour</b>                        | VVS:777568600<br>NRF:6311231<br>EAN:5708590146478<br>HMI: 25428<br>NBS:N13:436<br>White  |
| <b>Product description</b>           |  <p>PLUS handrails are high-quality products and they can be combined in countless ways and they provide the final touch to furnishing a functional and flexible bathroom. A reliable solution with many different options, which can easily lay the grounds for increased independence.</p> <p>PLUS handrail combination, 33 mm, reversible right/left, A: 762 mm x B: 762 mm x C: 1090 mm, for fixed mounting.<br/> The projection of 50 mm from the wall makes it easy to take hold of the rail.<br/> Inkl. wall rosette, which covers the fixings.<br/> Material: Powder-coated aluminium and plastic.<br/> Excl. mounting kit.</p> |
| <b>Product capacity</b>              | Maximum load: 235 kg.<br>When the handrail is loaded with 235 kg, each wall fastener is loaded with 56 kg.<br><i>Handrails are tested with a 1.5 safety factor in accordance with the requirements in ISO 17966:2016.</i>  |
| <b>Materials</b>                     | Basic material: Aluminium<br><br>Surface material: Polyester lacquer<br><br>Cover cap: Cycoloy plastic<br><br>Strap: Nylon (PA)  |
| <b>Ergonomy</b>                      | The 33 mm diameter enables the rail to be held comfortably and firmly. The projection of 50 mm from the wall makes it easy to take hold of the rail.   |
| <b>Warranty</b>                      | Pressalit makes a commitment to remedy material and manufacturing defects for a period of five years from the invoicing date.  |



# PRESSALIT®











|                                  |   |
|----------------------------------|---|
| <b>Product</b>                   | PLUS handrail corner with vertical grip 762 x 762 x 1090 mm   |
| <b>Item number</b>               | RT136000  |
| <b>Cleaning</b>                  | <p>Handrails ALU.</p> <p>The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based, corrosive or abrasive cleaners as it may result in the surface being damaged.</p> <p>The following cleaning agents have been tested by Pressalit and may be used, as long as they are diluted according to the instructions on the container.</p> <p><b>DISINFECTANTS:</b><br/>Clinimax Difficil-S<br/>Erisan OXY+</p> <p><b>NON-DISINFECTANTS:</b><br/>Suma Star free D1<br/>Taski 100<br/>Taski 200</p> <p>The product must be wiped down with a soft rag wrung out in clear water immediately after cleaning, as some materials may otherwise be discolored and stained, and the surface coating may deteriorate.</p> <p><b>DECALCIFICATION OF ALUMINUM PARTS:</b><br/>Pressalit recommends that chalky deposits be removed from wall tracks and other aluminum parts using a solution of three parts 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts must be wiped over with a damp cloth wrung out in clear water.</p> |
| <b>Declaration of conformity</b> | <p>CE UK MDR This product is in compliance with all relevant requirements of:<br/>- Regulation (EU) 2017/745 on medical devices.</p> <p><b>For the UK:</b> - Medical Device Regulation (MDR) 2002 on medical devices.</p>   |



PRESSALIT®











|                    |   |
|--------------------|---|
| <b>Product</b>     | PLUS handrail corner with vertical grip 762 x 762 x 1090 mm |
| <b>Item number</b> | RT136000  |

## Installation in different wall types

|   |  |
|---|--|
|    | <p><b>Concrete &gt;B25</b></p> <p>V8618 - Mounting kit, 16 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>    |
|   | <p><b>Solid Brick &gt;= Mz12</b></p> <p>V8618 - Mounting kit, 16 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>    |
|  | <p><b>Solid Sand Lime Brick &gt;= Hlz12</b></p> <p>V8618 - Mounting kit, 16 screws Ø5 x 50 - plugs SX8, for brick wall. Must be ordered separately.</p>                                     |
|  | <p><b>Aerated Concrete P4</b></p> <p>V8668 - Mounting kit, 16 bolts M5 x 50 - plugs FTP K 6. To be ordered separately.</p>    |
|  | <p><b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with wood</b></p> <p>V8618 - Mounting kit, 16 screws Ø5 x 50 - plugs SX8. NB! Plugs are not needed. To be ordered separately.</p>  |



# PRESSALIT®

|   |  |
|---|--|
| <b>Product</b><br><b>Item number</b>  | PLUS handrail corner with vertical grip 762 x 762 x 1090 mm<br>RT136000  |
|    | <p><b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with 22 mm plywood</b></p> <p>Wall fasteners (16 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.</p>          |
|    | <p><b>Drywall (2 x 12,5 mm) water-resistant, re-enforced with steel plates (2 mm)</b></p> <p>Wall fasteners (16 pcs) must be bought separately, for drywall it is possible to use e.g. fischer KD8 toggles or similar.</p>    |
|  | <p><b>Drywall (2 x 12,5 mm) water-resistant</b></p> <p>Mounting in this wall type is not recommended - risk of fatal injury to persons and walls.</p>   |

pressalit.com

Pressalit A/S  
 Pressalitvej 1  
 DK-8680 Ry  
 Tel.: +45 8788 8788  
 Fax: +45 8788 8789  
 E-mail: [pressalit@pressalit.com](mailto:pressalit@pressalit.com)

# PRESSALIT®