




Product	SELECT toilet lifter, manually height adjustable with crank handle, for floor outlet
Item number	R8017000
Colour	White
Product description	 <p>Discontinued per 9 Jan 2017 and replaced by R8012. Wallhung toilet 700 mm to be ordered separately (R2099).</p> <p>Toilet lifter, 300 mm height adjustable, with crank handle. Incl. cistern with dual flushing system preset at 3/6 litres, wall-hung toilet pan (pan projection 700 mm), and R27 white Dania toilet seat with extra strong cross-bar hinge D92. For floor-outlet. Materials: Anodised aluminium and polystyrene (PS). Incl. mounting kit for brick wall.</p> <p>Discontinued per 9 Jan 2017 and replaced by R8012. Wallhung toilet 700 mm to be ordered separately (R2099).</p> <p>Toilet lifter, 300 mm height adjustable, with crank handle. Incl. cistern with dual flushing system preset at 3/6 litres, wall-hung toilet pan (pan projection 700 mm), and R27 white Dania toilet seat with extra strong cross-bar hinge D92. For floor-outlet. Materials: Anodised aluminium and polystyrene (PS). Incl. mounting kit for brick wall.</p>
Adjustability	Height adjustable
Adjustment height	300 mm
Product capacity	Maximum load: 200 kg
Materials	The toilet lifter is mainly constructed of anodised aluminium. The front plate and the bottom plate are made of polystyrene (PS).
Ergonomy	Toilet lifters are available in three different colours which all harmonise with modern bathrooms, resulting in a comfortable and inviting toilet environment. A minimum of grooves, slots and holes makes cleaning fast and effective, and also results in an attractive and exclusive design.



PRESSALIT®

Product	SELECT toilet lifter, manually height adjustable with crank handle, for floor outlet
Item number	R8017000
Features	<p>The toilet can be raised and lowered using the crank handle. The crank handle can be positioned on either side of the lifter – without the need for tools.</p> <p>It is possible to adjust the height of the toilet lifter using an electric drill as an alternative to the crank handle.</p> <p>The toilet can be adjusted 300 mm, from 425 mm to 725 mm in height , so the height can always be perfectly matched to mobility aids such as a wheelchair.</p>
Cleaning	<p>Pressalit recommends that chalky deposits be removed from wall tracks and other aluminum parts using a solution of three parts of 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts should be wiped over with a damp cloth wrung out in clear water.</p>

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®