




PRESSALIT®

Product Item number	Changing table, 800 x 1400 mm, electrically height adjustable, with sanitary appliances R8754000
Colour Product description	<div> <div>White</div> <div>  </div> </div> <p>Discontinued per 31 Dec 2015 and replaced by R8654</p> <p>Freestanding changing table with sanitary appliances, 800 mm x 1400 mm, with electric motor with hand control incl. transformer. Incl. safety stop, integrated sink, tap, feed/waste system, 2 wire baskets. Height adjustable from 650 mm - 1000 mm. Excl. mounting kit.</p> <p>Discontinued per 31 Dec 2015 and replaced by R8654</p> <p>Freestanding changing table with sanitary appliances, 800 mm x 1400 mm, with electric motor with hand control incl. transformer. Incl. safety stop, integrated sink, tap, feed/waste system, 2 wire baskets. Height adjustable from 650 mm - 1000 mm. Excl. mounting kit.</p>
Adjustability Product capacity Speed upwards Noise level	Height adjustable Max load: 75 kg. Speed up mm: 14 mm/s Speed down mm: 14 mm/s 48 dB
Materials Ergonomy Features Mains connection (V) Actuator (motor)	Lifting unit and baskets: Powder-laquered steel. Worktop: ABS with acrylic. The smooth height adjustment ensures that it is always possible to set the table at an ergonomically correct height. Easy-to-clean surfaces ensure optimum hygiene. Integrated sink and tap with pull-out spout. 230 LA31 Deskline (Linak), 1500N, IPX1



PRESSALIT®

Product	Changing table, 800 x 1400 mm, electrically height adjustable, with sanitary appliances
Item number	R8754000
Control box	CBD6 (Linak), IP22
Wired remote control	HB3 (Linak), IP66
Power consumption (maximum load)	Power consumption by maximum load, watt: 96 W Power consumption by standby: 0,1 W
Cleaning	The product is to be cleaned with hot water or a mild soapy cleaning agent. Do not use chlorine based or corrosive cleaners as it may result in the surface being damaged.

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®